




## Roller/ Solar Minimum Mounting Depth Requirement

Product ID: 535414, 535415, 535419, 550237


Semi Inside Mount



Partially Protruding Out  
of the Window Opening

Lift System	Top Treatment	Single Shade (in)	Dual Shade (in)
Continuous Cord Loop*	None	3 1/4	2 3/4 with valance°
	Fascia	2 7/8	
Cordless	None	3 1/8	
	Fascia	2 5/8	
Motorization*	None	3 1/4	N/A
	Fascia	2 3/4	

Inside Mount



Flush with the Window Opening

Lift System	Top Treatment	Single Shade (in)	Dual Shade (in)
Continuous Cord Loop*	None	3 7/8	4 5/8 with valance°
	Fascia	4 1/4	
Cordless	None	3 1/2	
	Fascia	4 1/8	
Motorization*	None	3 5/8	N/A
	Fascia	4 1/8	

\* Coupled shades are available for these lifts and have the same depth as single shade.

°Valance is only available for Dual Shade

*Note: Inside Mount depth may be slightly different depending on the window size and the fabric.  
The above measurements are rounded to provide a simplified version. Please refer to the spec book for the exact minimum depths.*