


Sheer Minimum Mounting Depth Requirement

Product ID: 545481, 545495


Semi Inside Mount



Partially Protruding Out of the Window Opening

Lift System	Top Treatment	Minimum Depth (in)
Continuous Cord Loop Motorization	Fascia	3 3/4
	Valance	4 1/8

Inside Mount



Flush with the Window Opening

Lift System	Top Treatment	Minimum Depth (in)
Continuous Cord Loop	Fascia	4
	Valance	4 3/8
Motorization	Fascia	4 1/8
	Valance	4 5/8

The above measurements are rounded to provide a simplified version. Please refer to the spec book for the exact minimum depths.